PRIMABRITE BRILLIANT

Specification sheet





Primabrite Brilliant is a thin opaque offset paper specifically designed for the printing of pharmaceutical leaflets. Its high whiteness meets industry requirements as well as providing good opacity and excellent legibility. Primabrite Brilliant can be used in either reels or sheets.

FSC or **PEFC** on request

Specifications Specification Specification Specification Specification Specificat							
Characteristics	Unit	Standard					
Code			PBB40WI	PBB45WI	PBB50WI	PBB60WI	
Grammage	g/m²	ISO 536	40 g/m ²	45 g/m ²	50 g/m ²	60 g/m ²	
Thickness	μm	ISO 534	52	59	65	78	
Bulk	cm³/g	-	1.30	1.30	1.30	1.30	
CIE whiteness	%	ISO 11475	150	150	150	150	
Opacity	%	ISO 2471	80	80	81.5	85.5	
pH paper	-	ISO 6588	8.5	8.5	8.5	8.5	
Absolute humidity	%	NF Q03-003	5.3	5.3	5.3	5.3	
Permanent paper	-	ISO 9706	YES				
Optical brightner	-	-	YES				
Luminescence			12				

Paper tolerances			
Grammage: nominal value + / - 1 g/m²	CIE whiteness: minimum 145		
Thickness: nominal value + / - 2 μm	Opacity minimum: nominal value - 1 point		
Meets with REACH regulations	Suitable for food contact		

Finished goods tolerance

Joins: a maximum of 1 join per reel with a maximum 15% of the reels within any order containing joins. Joins are recorded on the delivery notes, on the reel label and also on the edge of the reel itself

Width: customer width - 0 mm, + 2 mm

Outer diameters of 100 cm, 114 cm or 120 cm: - 3 cm, + 2 cm

Conditions of storage and optimal use

When in stock the paper should be stored in its original packaging and storage temperatures should not drop below 15 $^{\circ}$ C The paper should be acclimatized in the workshop area it's to be used, ideally 24 or even 48 hours if possible before use Optimal conditions of the workshop are: 23 $^{\circ}$ C ±3 $^{\circ}$ C and 50% ±5% of relative humidity

Minimum making: Quantity required by the mill will be dependent on both the production schedules and the possibilities at the time of the order for a combination of widths to cover the machine deckle.

Please contact your sales representative for more details.

Validated: 02/09/2015

Qualified by Emmanuel Bruneau-Technical Support Manager